



COMPRESSED AIR TREATMENT
REDEFINED



FBP HL
FOOD BEV PHARMA

Parker Zander FBP - Food Beverage and Pharma. Innovative engineering and technology.

Combining sophisticated OIL-X filtration technology with an optimised drying system, the FDA approved FBP is designed to deliver consistent high performance over an extended period. It also offers class 0 for total oil and is FDA Title 21 CFR approved. Air quality is third-party validated to ISO 7183 and ISO 8573-1. So you can be completely confident of your compressed air quality.

ISO 8573-1
CLASS 0
AIR

The OFAS is third party validated by Lloyds register to provide ISO 8573-1 Class 0, with respect to total oil from both oil lubricated and oil free compressors, ensuring the highest quality air at the point of use for critical applications.

- › **Energy Saving Technology**
Standard on all units, it automatically adapts dryer operation to the ambient inlet conditions and compressed air demand, ensuring optimum energy consumption and full utilisation of the desiccant material.
- › **HMI display screen**
Large screen display offering a wealth of clear, useable, real-time information.
- › **High strength desiccant**
Cartridges are snowstorm filled with high strength desiccant that has a 5-year lifetime, providing consistent drying, re-generation and dewpoint.
- › **Pre-mounted filters**
New series OIL-X filters engineered to provide validated ISO 8573-1 performance.
- › **Threaded top end-cap**
Threaded end-cap enables the straightforward replacement of the desiccant cartridge.
- › **Purge setting**
The purge air can be set at minimum operating pressure easily, without the need for specialist tools.
- › **Corrosion protected column**
With a 10-year guarantee, to ensure a long operational life.
- › **Full bore internal flow paths**
Featuring optimised flow management for reduced pressure drop.
- › **Full bore cylinder valve system**
Low pressure loss valves provide full air flow and minimal back pressure, whilst robust cylinders extend service intervals.
- › **Base plate**
Designed for pallet trucks, allowing for easy, time-saving installation.
- › **3rd party certified for user peace of mind**
FDA Title 21 CFR
EC 1935/2004 Exemption

CFP - Correction Factor Minimum Inlet Pressure

Minimum Inlet Pressure	bar g	4	5	6	7	8	9	10	11	12	13	14	15	16
	psi g	58	73	87	100	116	131	145	160	174	189	203	218	232
Correction Factor		1.60	1.33	1.14	1.00	0.89	0.80	0.73	0.67	0.62	0.57	0.53	0.50	0.47

CFD - Correction Factor Dewpoint

Pressure Dewpoint	°C	-20	-40	-70
	°F	-4	-40	-100
Correction Factor		0.91	1	2.00

Technical Data

Dryer Models	Min Operating Pressure		Max Operating Pressure		Min Operating Temperature		Max Operating Temperature		Max Ambient Temperature		Electrical Supply (standard)	Electrical Supply (optional)	Filter Thread Connections	Noise Level
	bar g	psi g	bar g	psi g	°C	°F	°C	°F	°C	°F				
OFAS HL 50-85	4	58	16	232	5	41	50	122	55	131	85 - 265V 1ph 50/60Hz	24V DC	BSPP or NPT	<75

OIL-X Pre-Mounted Filters

Filtration Position	Inlet	Inlet	Outlet	Outlet
Filtration Grade	Grade AO	Grade AA	OVR	Grade AO
Filtration Type	Coalescing	Coalescing	Oil Vapour Removal	Dry Particulate
Particle Removal (inc water & oil aerosols)	Down to 1 micron	Down to 0.01 micron	N/A	Down to 1 micron
Maximum Remaining Oil Content at 21°C	0.5 mg/m ³ (0.5 ppm(w))	0.01 mg/m ³ (0.01 ppm(w))	0.003mg/m ³ at system temperature (0.003ppm(w)) at system temperature	N/A
Filtration Efficiency	99.925%	99.9999%	N/A	99.925%

Weight & Dimensions

Model	Port Connection Inlet / Outlet	Dimensions						Weight		Inlet		Outlet
		Height (H)		Width (W)		Depth (D)				General Purpose Coalescing Filter	High Efficiency Coalescing Filter	General Purpose Dry Particulate Filter
		mm	ins	mm	ins	mm	ins	kg	lbs			
OFAS HL 50	½"	1133	45	559	22	512	20.2	90	198	AOP015C	AAP015C	AOP015C
OFAS HL 55	½"	1313	52	559	22	512	20.2	97	214	AOP015C	AAP015C	AOP015C
OFAS HL 60	½"	1510	59	559	22	496	19.5	106	234	AOP020C	AAP020C	AOP020C
OFAS HL 65	½"	1660	65	559	22	496	19.5	112	247	AOP020C	AAP020C	AOP020C
OFAS HL 70	¾"	2020	80	559	22	496	19.5	132	291	AOP025D	AAP025D	AOP025D
OFAS HL 75	1"	1595	63	559	22	682	27	184	406	AOP025E	AAP025E	AOP025E
OFAS HL 80	1"	1745	69	559	22	682	27	196	432	AOP025E	AAP025E	AOP025E
OFAS HL 85	1½"	2105	83	559	22	682	27	232	511	AOP030G	AAP030G	AOP030G

Pressure Vessel Approvals

Developed and Manufactured to DIN EN ISO 9001, DIN EN ISO 14001.

Pressure vessel approved for fluid group 2 in accordance with the Pressure Equipment Directive 2014/68/EU and AS1210.

Approval to ASME VIII Div. 1 not required. For use with Compressed Air and Gaseous Nitrogen.

For more information please contact your local sales office or visit www.parker.com/gsf

Parker has a continuous policy of product development and although the company reserves the right to changes specifications, it attempts to keep customers informed of any alterations.

Parker Worldwide

Europe, Middle East, Africa

AE – United Arab Emirates,
Dubai

Tel: +971 4 8127100
parker.me@parker.com

AT – Austria, Wiener Neustadt
Tel: +43 (0)2622 23501-0
parker.austria@parker.com

AT – Eastern Europe, Wiener
Neustadt
Tel: +43 (0)2622 23501 900
parker.easteurope@parker.com

AZ – Azerbaijan, Baku
Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/LU – Belgium, Nivelles
Tel: +32 (0)67 280 900
parker.belgium@parker.com

BG – Bulgaria, Sofia
Tel: +359 2 980 1344
parker.bulgaria@parker.com

BY – Belarus, Minsk
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

CH – Switzerland, Etoy
Tel: +41 (0)21 821 87 00
parker.switzerland@parker.com

CZ – Czech Republic, Klecany
Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst
Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup
Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid
Tel: +34 902 330 001
parker.spain@parker.com

FI – Finland, Vantaa
Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve
Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Athens
Tel: +30 210 933 6450
parker.greece@parker.com

HU – Hungary, Budaörs
Tel: +36 23 885 470
parker.hungary@parker.com

IE – Ireland, Dublin
Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IL – Israel
Tel: +39 02 45 19 21
parker.israel@parker.com

IT – Italy, Corsico (MI)
Tel: +39 02 45 19 21
parker.italy@parker.com

KZ – Kazakhstan, Almaty
Tel: +7 7273 561 000
parker.easteurope@parker.com

NL – The Netherlands, Oldenzaal
Tel: +31 (0)541 585 000
parker.nl@parker.com

NO – Norway, Asker
Tel: +47 66 75 34 00
parker.norway@parker.com

PL – Poland, Warsaw
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal
Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest
Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow
Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga
Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SK – Slovakia, Banská Bystrica
Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto
Tel: +386 7 337 6650
parker.slovenia@parker.com

TR – Turkey, Istanbul
Tel: +90 216 4997081
parker.turkey@parker.com

UA – Ukraine, Kiev
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

UK – United Kingdom, Warwick
Tel: +44 (0)1926 317 878
parker.uk@parker.com

ZA – South Africa, Kempton Park
Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

North America

CA – Canada, Milton, Ontario
Tel: +1 905 693 3000

US – USA, Cleveland
Tel: +1 216 896 3000

Asia Pacific

AU – Australia, Castle Hill
Tel: +61 (0)2-9634 7777

CN – China, Shanghai
Tel: +86 21 2899 5000

HK – Hong Kong
Tel: +852 2428 8008

IN – India, Mumbai
Tel: +91 22 6513 7081-85

JP – Japan, Tokyo
Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul
Tel: +82 2 559 0400

MY – Malaysia, Shah Alam
Tel: +60 3 7849 0800

NZ – New Zealand, Mt Wellington
Tel: +64 9 574 1744

SG – Singapore
Tel: +65 6887 6300

TH – Thailand, Bangkok
Tel: +662 186 7000

TW – Taiwan, Taipei
Tel: +886 2 2298 8987

South America

AR – Argentina, Buenos Aires
Tel: +54 3327 44 4129

BR – Brazil, Sao Jose dos Campos
Tel: +55 800 727 5374

CL – Chile, Santiago
Tel: +56 2 623 1216

MX – Mexico, Toluca
Tel: +52 72 2275 4200

European Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI,
FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU,
SE, SK, UK, ZA)



Parker Hannifin Ltd.

Tachbrook Park Drive
Tachbrook Park,
Warwick, CV34 6TU
United Kingdom
Tel.: +44 (0) 1926 317 878
Fax: +44 (0) 1926 317 855
parker.uk@parker.com
www.parker.com/gsf

SARLIN

SARLIN OY AB • PL 750, 00101 Helsinki
Käyntiosoite: Kaivokselantie 3, 01610 Vantaa
Vaihde 010 550 4000 • Fax 010 550 4201
info@sarlin.com • www.sarlin.com